EMERGENCY EYEWASH & SHOWER EQUIPMENT

FENDALL PORTA STREAM® I EYEWASH STATIONS

- · Delivers 6 minutes of flushing fluid
- Easy installation with no plumbing required
- Single bracket mounting device included
- One-piece, molded construction with no moving parts
- Large hole simplifies refilling and cleaning
- Features simple, highly visible instructions on the unit itself
- Does not meet ANSI standard Z358.1 15-minute flushing requirement



FENDALL PORTA STREAM® II EYEWASH STATIONS

- Versatile portability and 15-minutes of uninterrupted flushing - without costly plumbing
- Simple installation and operation
- Features a nozzle strap that is easily removed to activate flushing, leaving hands free to hold eyelids open
- Can be easily and affordably placed near most workplace hazards with single bracket mounting device or transported with optional universal cart or universal stand
- Moulded handle accepts hanging bracket for vertical or horizontal surface installation
- Versatile flushing fluid options include Eyesaline® a preserved, buffered, saline solution superior to tap water for emergency eye care, and water additive
- Large 16-gallon (60.5 L) capacity
- SEI certified to meet ANSI standard Z358.1



SEK529

Honeywell

Model No.	Mfg. No.	Description	Wt. Ibs.	Price /Each
SA425	32-000100-0000	Fendall Porta Stream® I, Trilingual instructions	19	
SA408	32-000509-0000	Eyesaline® concentrate, 70 oz. (For Porta Stream® I)	5	
SAJ677	32-001100-0022	Water Preservative, 4 - 8 oz. bottles	-	
SA426	32-000102-0000	Replacement pull-strap, (Fits Porta Stream® I, II, III)	1	

Honeywell

Model No.	Mfg. No.	Description	Wt. Ibs.	Price /Each
SEK529	32-000200-0000	Trilingual Instructions	36	
SA411	32-000513-0000	Eyesaline® Concentrate, 180 oz.	13	
SAJ677	32-001100-0022	Water Preservative, 4 - 8 oz. Bottles	-	
SA426	32-000102-0000	Replacement Pull-Strap, (Fits Porta Stream® I, II)	1	

FENDALL FLASH FLOOD® EYEWASH STATIONS

- · Delivers 3 minutes of flushing fluid
- One-gallon sealed cartridges are easy to store and offer quick changes without mixing or measuring
- · Easily wall or table mounted
- Features simple, highly visible instructions on the unit itself
- Does not meet ANSI standard Z358.1 15-minute flushing requirement

Honeywell

Model No.	Mfg. No.	Description	Wt. lbs.	Price /Each
SA419	32-000400-0000	Fendall Flash Flood® Eyewash Station (English Instructions)	14	
SAM657	32-000400-0022	Fendall Flash Flood® Eyewash Station (French Instructions)	14	
SA403	32-000401-0000	Eyesaline® 1 Gal. Refill (4/Pkg.) (English Instructions)	36	
SAM658	32-000401-0022	Eyesaline® 1 Gal. Refill (4/Pkg.) (French Instructions)	36	
SA420	32-000402-0000	Wire Rack for Cartridges	3	
SA421	32-000403-0000	Replacement Pull Strap	1	



EYEWASH STATIONS

- Recommended for use in workplaces, industry, laboratories, schools, garages and food processing plants
- · Acrylic mirror to assist the user
- Wall mountable
- Does not meet ANSI standard Z358.1 15-minute flushing requirement

SAY483



Model Mfg. No. No. Description SAY483 04074 Plastic station w/one 946 ml empty eyewash bottle SAY487 Metal station w/one 946 ml empty eyewash bottle SAY484 04066 Plastic station w/one 1 L eyewash solution **SAY489** 04068 Metal station w/one 1 L eyewash solution SAY485 Plastic station w/two 946 ml empty eyewash bottle 04757 SAY486 Plastic station w/two 1 L eyewash solution 04067

EYEWASH BOTTLES

STERILE

- · Ready-to-use solution for eye irrigation
- Cleanses the eye to help relieve irritation, discomfort, burning, stinging, smarting or itching by removing loose, foreign material, air pollutants (smog or pollen) or chlorinated water



Model	Mfg.		Price
No.	No.	Size	/Each
SAY477	04076	500 ml	
SAY478	04077	1L	
SAY479	04078	4 L	